

### UV/LD/b Series

THERMOLAST® K

The UV/LD/b Series is your material solution for applications requiring high UV resistance. It is particularly appropriate for automotive exterior.

#### **Typical applications**

- · Cowls gaskets
- · Roof rims
- Water deflectors
- · Window encapsulations

#### **Material advantages**

- Excellent heat resistance
- · Excellent mechanical properties
- · Perfect adhesion to PP
- · Perfect surface finish
- Tested according PV3930 for outdoor use

Processing Method: Extrusion, Injection Molding

	Color / RAL DESIGN	Hardness DIN ISO 7619-1 ShoreA	Hardness DIN ISO 7619-1 ShoreD	Density DIN EN ISO 1183-1 g/cm3	<b>Tensile Strength</b> DIN 53504/ISO 37 MPa	Elongation at Break <sup>1</sup> DIN 53504/ISO 37 %	<b>Tear Resistance</b> ISO 34-1 Methode B (b)(Graves) N/mm	<b>CS 72 h/23 °C</b> DIN ISO 815-1 Method A %	<b>CS 24 h/70 °C</b> DIN ISO 815-1 Method A %	<b>CS 24 h/100 °C</b> DIN ISO 815-1 Method A %
TP3LDZ	black	32		0.970	5.5	800	8.0	14	30	52
TP4LDZ	black	42		0.970	7.0	800	11.0	16	29	43
TP5LDZ	black	52		0.970	8.5	800	14.0	22	35	49
TP6LDZ	black	63		0.970	9.5	750	18.0	27	40	55
TP7LDZ	black	71		0.970	10.5	750	22.0	30	44	58
TP8LDZ	black	79		0.970	13.5	750	28.0	31	44	61
TP9LDZ	black	82		0.970	16.0	750	32.0	40	60	77
TP0LDZ	black		35	0.970	21.0	700	58.0	-	-	-

<sup>&</sup>lt;sup>1</sup> Deviating from ISO 37 standard test piece S2 is tested with a traverse speed of 200 mm/min.

All values published in this data sheet are rounded average values.

This datasheet is an extract of the KRAIBURG TPE program. Please contact KRAIBURG TPE to select the compound suitable for the requirements.




UV/LD/b Series THERMOLAST® K

#### **Compression Set**

## Compression Set (acc. DIN ISO 815)

For the compression set testing the following specimen is used: The specimen is a cylindrical disk shaped 6 mm thick and 13 mm in diameter.



The specimen is compressed by 25%. The compressed specimen is heated to the test temperature. DIN ISO 815 discribes two methods.

**Method A:** The specimen is allowed to recover immediately after its aging in the oven and then cooled down to room temperature. After 30 minutes the thickness of the specimen is measured and the compression set calculated.

**Method B:** The specimen is cooled down to room temperature after its aging in the oven and then allowed to recover.

Test results gained from method B are in general higher than from method A.

This datasheet is an extract of the KRAIBURG TPE program. Please contact KRAIBURG TPE to select the compound suitable for the requirements.



## UV/LD/b Series

# THERMOLAST® K

Cylinder temperature	180 - 200 - 220 °C, max. 250 °C (360 - 390 - 430 °F, max. 480 °F)				
Cylinder temperature	100 - 200 - 220 C, max. 230 C (300 - 390 - 430 T, max. 400 T)				
Hotrunner	Hot runner temperatures: 200 -250 °C (390 - 480 °F). The runner should be empty after a maximum of 2 - 3 shots.				
Injection pressure	200 - 1000 bar (2900 - 14504 psi) (depending on the size and weight of the part).				
Injection rate	In general, the fill time should not be more than 1–2 seconds.				
Hold pressure	We recommend to derive the optimum hold pressure from determining the solidification point, starting with 40 % - 60 % of the required injection pressure.				
Back pressure	20 - 100 bar; if color batches are used, higher back pressure is necessary.				
Screw retraction	If an open nozzle is used processing with screw retraction is advisable.				
Mold temperature	25 - 40 °C (77 - 104 °F)				
Predrying	Pre drying of the material is not necessary; if surface moisture forms as a result of changes in temperature, the material should be dried for 2 - 4 hours at 60 - 80 °C (140 - 175 °F).				
Needle valve	With materials < 50 Shore A the use of a needle valve is advisable.				
Screw geometry	Standard 3-zone polyolefine screw.				
Residence time	The residence time is to be set as short as possible with a maximum of 10 minutes.				
Cleaning recommendation	For cleaning and purging of the machine it is appropriate to use polypropylene or polyethylene. Machine must be PVC-free.				

This datasheet is an extract of the KRAIBURG TPE program. Please contact KRAIBURG TPE to select the compound suitable for the requirements.



## UV/LD/b Series

# THERMOLAST® K

Processing Guideline Extrusion						
Cylinder temperature	160 - 180 - 200 °C, max. 250 °C (320 - 360 - 390 °F; max. 480 °F)					
Screw geometry	Standard three-zone screw (e.g. polyolefin screw). The screw must be able to provide sufficient shearing.					
L/D ratio	At least 25					
Compression ratio	At least 3.5 : 1					
Screens / breaker plate	A breaker plate and a screen pack are generally recommended in the extruder configuration in order to increase pressure.					
Die land	<= 3 mm ( <= 0,12 in.)					
Extruder Head	Ca. 200 °C (390 °F)					
Die temperature	Ca. 200 - 230 °C (390 - 450 °F)					
Predrying	Pre drying of the material is not necessary; if surface moisture forms as a result of changes in temperature, the material should be dried for 2 - 4 hours at 60 - 80 °C (140 - 175 °F).					
Calibration	Generally not necessary; support elements may be required when extruding THERMOLAST® compounds with high hardness or when coextruding with standard thermoplastics.					
Cleaning recommendation	For cleaning and purging of the machine it is appropriate to use polypropylene or polyethylene. Machine must be PVC-free.					

This datasheet is an extract of the KRAIBURG TPE program. Please contact KRAIBURG TPE to select the compound suitable for the requirements.